

# **MOTIP Alu-Zinc Spray**

Ord.-no.: 04059



## **Technical Information**

Fast-drying Alu-Zinc Spray with good filling properties and excellent adhesion to treat galvanised and untreated steel. Alu-Zinc Spray offers outstanding cathodic corrosion prevention, is spot-weldable and is resistant to petrol, chemicals and the weather. MOTIP Alu-Zinc Spray is heat resistant to 250°C.

## **Quality & properties**

- Outstanding cathodic corrosion prevention
- Good filling property
- Resistant to petrol, chemicals and weather influences
- Fast drying
- Spot-weldable
- Excellent adhesion

### Physical & chemical data

Base: Epoxy-esterColourname: Alu-silver

• Degree of gloss: mat, 10 ±2 GU

• Efficiency: 400 ML – 1.25 -1.75 m<sup>2</sup>

• Dry to touch: 20-30 min

• Dust dry: 10-15 min

Completely dry: 24 h

Overcoatable: 24 h

• Surfaces: Treat galvanised and untreated steel.

Minimum Working Temperature: 10 °C

Maximum Working Temperature: 25 °C

Vapour pressure: 4000/20 bar

• Storage stability: 10 years

Content: 400 ML

#### How to use

- Before use, carefully read the directions on the packaging and act accordingly.
- The surface should be clean, dry and free of grease. Remove loose old lacquer and rust and sand the surface
- The surface should be clean, dry and free of grease. The aerosol should have room temperature. Best processing temperature 15 to 25°C.
- Before use, shake the aerosol for 2 minutes and spray a sample. Distance to the surface to be treated approximately 25 to 30 centimetre.
- Apply the alu-zinc spray in several thin layers. Before applying the next layer, again shake the aerosol. When desired, after drying a primer and a lacquer can be applied.
- After use, clean the valve (turn aerosol upside down and press the nozzle for approximately 5 seconds).
- The drying time depends on the ambient temperature, the humidity of the air and the thickness of the lacquer applied.

# **Environmentally sound**

European Aerosols is committed to apply formulations without restricted or critical ingredients and to achieve best possible performance. The caps and packagings are made of recyclable material.

#### Disposa

Only the completely emptied cans should be put into the recycling skip or appropriate container for reclaimable refuse. Cans which are not empty should be disposed off as "special refuse".

#### Marking/Labelling

All products made by European Aerosols comply with the actual labelling regulations according to Preparation Guideline 1999/45/EG. All aerosols correspond to TRGS 200 and TRG 300 as well as to aerosol guideline 75/324/EWG in the actually valid version.

For any further technical questions call our hotline +31 (0) 561 69 44 00 from Monday to Thursday from 9 h a.m. to 3 h p.m. or on Friday until 12 h p.m.

As of November 24, 2021 – This release replaces all eventually earlier issued versions.

European Aerosols GmbH, Kurt-Vogelsang-Straße 6, 74855 Haßmersheim - info-de@european-aerosols.com European Aerosols B.V., Wolfraamweg 2, NL-8471 XC Wolvega - info-nl@european-aerosols.com